

Laser Blade XS


Design iGuzzini

iGuzzini

Last information update: June 2025

Product configuration: QI95

QI95: Minimal 3 cells - Medium beam - LED



Product code

QI95: Minimal 3 cells - Medium beam - LED

Technical description

Linear miniaturised recessed luminaire with 3 optical elements for LED lamps - fixed optic. Despite the ultracompact size of the product, the patented technology of the optic system guarantees an efficient luminous flux and a high level of controlled glare visual comfort. Main body with die-cast zamak radiant surface, minimal (frameless) version for mounting flush with the ceiling. For recessed installation in a false ceiling a specific adapter is required that is available with a separate item code. Metallised, thermoplastic, high definition Opti Beam reflector, integrated in a set-back position in the anti-glare screen. Ballast not included, available with separate code.

Installation

The luminaire is recessed in the specific adapter (QJ88) by means of a steel wire spring, previously installed on the ceiling that can be 12.5 / 15 / 20 mm thick. A special protective sheath allows finishing operations on the plasterboard to be simplified and speeded up.

Colour

White (01) | Black (04) | Gold (14)* | Burnished chrome (E6)*

Weight (Kg)

0.1

* Colours on request

Mounting

wall recessed|ceiling recessed

Wiring

Constant current ballasts to be ordered separately: ON-OFF - code no. MXF9 (min 1 / max 2); dimmable DALI - code no. BZM4 (min 1 / max 6) - check the instruction sheet for the lengths and compatible cross-sections of the cables to be used.

Notes

The special steel wire spring provided is required to facilitate the eventual extraction of the recessed body once it has been inserted.

Complies with EN60598-1 and pertinent regulations



Technical data

Im system:	427	CRI (minimum):	90
W system:	6	Colour temperature [K]:	2700
Im source:	540	MacAdam Step:	2
W source:	6	Life Time LED 1:	> 50,000h - L80 - B10 (Ta 25°C)
Luminous efficiency (Im/W, real value):	71.1	Lamp code:	LED
Im in emergency mode:	-	Number of lamps for optical assembly:	1
Total light flux at or above an angle of 90° [Lm]:	0	ZVEI Code:	LED
Light Output Ratio (L.O.R.) [%]:	79	Number of optical assemblies:	1
Beam angle [°]:	25°	LED current [mA]:	700


Polar

<p>Imax=1971 cd α=24°</p>	CIE nL 0.79 100-100-100-100-79 UGR <10-<10 DIN A.61 UTE 0.79A+0.00T F*1=999 F*1+F*2=1000 F*1+F*2+F*3=1000 CIBSE LG3 L<1500 cd/m² at 65° UGR<10 L<1500 cd/mq @65°	Lux			
		h	d	Em	E _{max}
		2	0.9	409	493
		4	1.7	102	123
		6	2.6	45	55
		8	3.4	26	31

Utilisation factors

R	77	75	73	71	55	53	33	00	DRR
K0.8	71	68	65	63	67	65	64	62	78
1.0	75	71	69	67	70	68	68	66	83
1.5	78	76	74	72	75	73	72	70	89
2.0	81	79	77	76	78	76	76	73	93
2.5	82	81	80	79	80	79	78	76	96
3.0	83	82	81	81	81	80	79	77	98
4.0	84	83	83	82	82	82	80	79	99
5.0	84	84	84	83	83	82	81	79	100

Luminance curve limit



UGR diagram

Corrected UGR values (at 540 lm bare lamp luminous flux)											
Reflect.: ceiling/cav walls work pl. Room dim x y		0.70	0.70	0.50	0.50	0.30	0.70	0.70	0.50	0.50	0.30
		0.50	0.30	0.50	0.30	0.30	0.50	0.30	0.50	0.30	0.30
		0.20	0.20	0.20	0.20	0.20	0.20	0.20	0.20	0.20	0.20
		viewed crosswise					viewed endwise				
2H	2H	3.0	5.1	3.4	5.4	5.8	3.0	5.1	3.4	5.4	5.8
	3H	2.8	4.4	3.2	4.8	5.1	2.8	4.4	3.2	4.8	5.1
	4H	2.8	4.1	3.2	4.4	4.8	2.8	4.1	3.2	4.4	4.8
	6H	2.7	3.8	3.1	4.1	4.5	2.7	3.8	3.1	4.1	4.5
	8H	2.7	3.7	3.1	4.1	4.4	2.7	3.7	3.1	4.1	4.4
	12H	2.7	3.7	3.1	4.0	4.4	2.6	3.7	3.0	4.0	4.4
4H	2H	2.8	4.1	3.2	4.4	4.8	2.8	4.1	3.2	4.4	4.8
	3H	2.6	3.7	3.0	4.0	4.4	2.6	3.7	3.0	4.0	4.4
	4H	2.5	3.5	2.9	3.9	4.3	2.5	3.5	2.9	3.9	4.3
	6H	2.2	3.9	2.7	4.3	4.8	2.2	3.9	2.6	4.3	4.8
	8H	2.1	3.9	2.5	4.4	4.9	2.0	3.9	2.5	4.4	4.9
	12H	2.0	3.9	2.5	4.4	4.9	1.9	3.9	2.4	4.4	4.9
8H	4H	2.0	3.9	2.5	4.4	4.9	2.1	3.9	2.5	4.4	4.9
	6H	1.9	3.7	2.4	4.2	4.7	2.0	3.7	2.5	4.2	4.8
	8H	1.9	3.5	2.5	4.0	4.6	1.9	3.5	2.5	4.0	4.6
	12H	2.1	3.1	2.7	3.6	4.2	2.1	3.1	2.6	3.6	4.2
12H	4H	1.9	3.9	2.4	4.4	4.9	2.0	3.9	2.5	4.4	4.9
	6H	1.9	3.5	2.4	4.0	4.5	2.0	3.5	2.5	4.0	4.6
	8H	2.1	3.1	2.6	3.6	4.2	2.1	3.1	2.7	3.6	4.2
Variations with the observer position at spacing:											
S =	1.0H	6.9 / -11.5					6.9 / -11.5				
	1.5H	9.7 / -11.7					9.7 / -11.7				
	2.0H	11.7 / -11.8					11.7 / -11.8				